


FEATURES

- **IP66 Rating:** Ensures protection against dust and powerful water jets, suitable for outdoor and industrial environments.
- **Dimming Operations:** Compatible with DALI2, Push Dimming, and PWM, providing versatile lighting control options.
- **High Driver Current:** Capable of delivering up to 15 A, supporting high-power LED applications.
- **Wide Input Voltage Range:** Operates efficiently with an input voltage of 200 to 240 V AC, suitable for various regions.
- **Single Output:** Simplifies installation and reduces complexity in lighting systems.

RS PRO 360W LED Driver, 24V Constant Voltage

RS Stock No: 642-784



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO LED Driver provides a reliable power solution for LED lighting systems, delivering a constant voltage output of 24V. Designed to handle a maximum output power of 360W, it is ideal for high-demand applications requiring stable and efficient power delivery. The driver supports various dimming operations, including DALI2, Push Dimming, and PWM, offering flexibility in lighting control.

General Specifications

Dimming Operation	DALI2, Push Dimming, PWM
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

Electrical Specifications

Driver Current	15 A
Input Voltage	200-240 V ac
Input Voltage Type	AC
Maximum Output Power	360 W
Output Voltage	24 V

Protection Category

IP Rating	IP66
-----------	------

Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, EN61000-3-3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547, EN62493, UL8750
---------------------	--