


340TX T27H X120 Wood-Compo TORX Screwdriver

Does not slip even when oily.



- Extraordinary non-slip grip; Secures working efficiency even with oily hands.
- Wood-composite resin, reproducing the natural material texture.
- Only 3% less torque rate with slippery and oily hands compared to dry using
- Anti-corrosion black chrome plated blade CR-V
- Non-electrolytic plating, keeping the precise tip quality.
- Also good for tamper-proof TORX screws.
- The magnetizes tip allows comfortable screwing
- TORX is a registered trademark of Acument TM Intellectual Properties, LLC (USA).
- VESSEL has a manufacturing license in Japan and selling same to the world.

PRODUCT SPECIFICATION

Index	Modèle	Product	Tip TORX	Tip O/D	Tip mm	Tip mm	Tip mm	Tip mm	Inner C/T	Outer C/T	EAN
120081	340TX T10H X80	Wood Compo Torx Tamper Proof T10H 80mm	T10H	2.72	80	5.5	30	188	6	120	4907587075109
120082	340TX T15H X80	Wood Compo Torx Tamper Proof T15H 80mm	T15H	3.26	80	5.5	30	188	6	120	4907587075116
120083	340TX T20H X120	Wood Compo Torx Tamper Proof T20H 120mm	T20H	3.84	120	5.5	30	228	6	120	4907587075123
120084	340TX T25H X120	Wood Compo Torx Tamper Proof T25H 120mm	T25H	4.40	120	6.4	32	236	6	60	4907587075130
120085	340TX T27H X120	Wood Compo Torx Tamper Proof T27H 120mm	T27H	4.96	120	6.4	32	236	6	60	4907587075147
120086	340TX T30H X120	Wood Compo Torx Tamper Proof T30H 120mm	T30H	5.49	120	8.0	35	246	6	60	4907587075154
120087	340TX T40H X120	Wood Compo Torx Tamper Proof T40H 120mm	T40H	6.60	120	8.0	35	246	6	60	4907587075161