



Chemical protection

# ULTRANITRIL 475

Flocked | intermittent wear



CHEMICAL PROTECTION  
**TYPE B**

EN388



3001X

EN ISO 374-1



TYPE B  
JOT

EN ISO 374-5



CATEGORY 3



0334

DEXTERITY

EN420:  
5/5



Completely liquidproof and very good resistance for food handling

## SPECIFIC ADVANTAGES



### Comfort

- Excellent dexterity, due to the suppleness of the glove



### Productivity

- Good grip due to the embossed exterior finish



### Skin protection

- Recommended for people sensitive to the proteins in natural latex



### Food compliance

- Suitable for all type of food



### Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



### Care for the environment

- Plastic packaging optimized
- Recycled material in the packaging: 30 %

## INDUSTRIES

- Food industry

## APPLICATIONS

- Cutting meat and fish
- Food handling
- Food preparation
- Handling fruits and vegetables







Chemical protection

# ULTRANITRIL 475

Flocked | intermittent wear

## LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
3 0 0 1 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN ISO 374-1	CHEMICAL RISKS
	J: n-Heptane O: Ammonia 25% T: Formaldehyde 37%
TYPE B	
EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi
	FOOD CONTACT
	French decree of 05/08/2020

## PRODUCT DETAILS

Interior finish	Flocked
Exterior finish	Embossed texture
Material	Nitrile
Cuff characteristic	Straight cuff
Colour.s	Blue
Length (cm)	31
Thickness (mm)	0.34
European sizes	6 7 8 9 10
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	7.5E+10 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	3.0E+9 Ω

## LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 72 pairs/carton
-----------	---

## LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/08/18/1644
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France