

# Product information

## 12Vmax Impact Wrench CXT



### TW140DWAE

Nut Busting Torque	270 Nm
Battery Type	Lithium-ion
Battery Quantity (2.0Ah)	2
Voltage	12 v
Driving Shank	3/8" Square
Impacts per minute	0 - 3200 ipm
Standard Bolt	M8-M16
High Tensile Bolt	M6-M12
Noise sound pressure	88 dB(A)
Noise sound power	99 dB(A)
Noise K factor	3 dB(A)
No Load Speed	0 - 2600 rpm
Max Fastening Torque	140 Nm
Vibration: Fastening Bolt	8.0 m/sec <sup>2</sup>
Vibration K factor	1.5 m/sec <sup>2</sup>
Net weight	1.0 - 1.2 kg



**STANDARD EQUIPMENT:** 197396-9 Battery BL1021B, DC10WD 12Vmax Standard Charger, Belt clip

- Electric brake
- Variable speed control by trigger
- Forward / reverse rotation
- LED job light
- Ergonomic soft grip
- Belt clip

Details correct as of: 6-9-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)