

PRODUCT-DETAILS

204212

RING TERM CU 12-4 AWG 1/4 BOLT



General Information

Extended Product Type	204212
Product ID	7TAI029020R0005
EAN	5414363111641
Catalog Description	RING TERM CU 12-4 AWG 1/4 BOLT
Long Description	Insulation Piercing Magnet Wire Ring Terminal, Length 1.58 Inches, Width .50 Inches, Length of Teeth .61 Inches, Width of Teeth .53 Inches, Stud Size 1/4 Inch, Wire Range #12 AWG - #4 AWG 10,380 Circular Mil Area - 52,480 Circular Mil Area, Copper Alloy, Tin Plated

Ordering

EAN	5414363111641
UPC	786210867632

Dimensions

Product Net Length	0, mm
--------------------	-------

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	4.5 in 114 mm

Package Level 1 Height	3 in 76 mm
Package Level 1 Depth / Length	5 in 127 mm
Package Level 2 Units	500 piece
Package Level 2 Width	5.5 in 140 mm
Package Level 2 Height	4 in 102 mm
Package Level 2 Depth / Length	23.9 in 607 mm

Additional Information

Application	For aluminum to copper, aluminum to aluminum or copper to copper magnet wire connections.
Brand / Label	Sta-Kon
Effective Date	19710507
Material	Copper
Number of Batteries	0
Product Name	ELECTRICAL TERMINAL
Product Type	Ring Terminal
Special Functions	Designed to penetrate magnet wire insulation during application, eliminating the need for stripping, brazing, welding or other methods of joining magnet wire.
Standards	UL E9809

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	204212
Instructions and Manuals	204212

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
ETIM 7	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

