

Flexible unsupported neoprene work gloves, guarding against varied chemicals and solvents

- **Heightened flexibility:** AlphaTec® 29-500 industrial gloves' mix of neoprene and rubber maintains its elasticity, even at lower temperatures
- **Elevated comfort:** As they are lined with pure cotton flocking, they provide better perspiration absorption, ensuring greater wearer comfort
- **Reduced hand fatigue:** Due to their blend of neoprene and natural rubber, they ensure lightweight hand protection that is less tiring with sustained wear
- **Enhanced defenses:** Their unique formulation makes these safety gloves resistant to a wide range of acids, caustics, alcohols and solvents
- **Assured antistatic capabilities:** AlphaTec® 29-500 chemical-resistant gloves also comply with EN1149 antistatic standards

Industries

- Automotive
- Automotive Aftermarket
- Chemical

Applications

- Chemical Handling
- Maintenance
- General Purpose Auto Aftermarket



Previously known as: NEOTOP™ 29-500

Key Features

- **Neoprene coating:** For flexible, cold-resistant hand protection
- **Pure cotton flocking:** Perspiration absorption, for greater comfort
- **Natural rubber content:** Lighter weight, for lesser hand fatigue

Vulcanization Chemical Accelerators

- Diphenyl guanidine
- Diphenyl thiourea
- Natural rubber proteins
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards

EN ISO 374-1:2016



AKLNPT

EN ISO 374-5



VIRUS

EN388: 2016



2101A



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGT H	COLOR	PACKAGE
AlphaTec® 29-500	Liner Material: N/A Coating Material: Natural Rubber Latex and Neoprene Blend	7, 8, 9, 10, 11	300 / 11.8	Black	• 12 pairs per bag, 12 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.