



P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

AS SHOWN L000697-01
ANTENNA WITH REEL PACKAGING
REFERENCE ONLY



[FOR REFERENCE] DA PACKAGE

- NOTES.
- 1. UNLESS OTHERWISE SPECIFIED TOLERANCE PER EIA-481-D
 - 2. ORIENT PARTS AS SHOWN.
 - 3. MATERIAL : P.S 0.35mm THICKNESS, COLOR : BLACK, CONDUCTIVE
WHEN ALTERNATIVEMATERIAL (PET, P.P) USE, CONSULT ECO PRIOR TO MANUFACTURER.
 - 4. Q'TY/REEL : 500 PCS/REEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW.PARK	04JUN2024	 TE Connectivity	
		CHK SJ.NOH	04JUN2024		
		APVD Ng.WEITAT	04JUN2024	NAME Ceramic Patch ant, 2400-2500MHz, 12x12x4	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-160936	
				APPLICATION SPEC -	
				WEIGHT -	
MATERIAL SEE NOTE 3		FINISH -		SIZE A3	
				CAGE CODE 00779	
				DRAWING NO C-L000697	
				RESTRICTED TO -	
				SCALE 2:1	
				SHEET 2 OF 4	
				REV A	
				CUSTOMER DRAWING	

ANTENNA WITH EVB ASS'Y




1. MATERIAL : SEE TABLE.
2. FINISH : EVB ASSEMBLY WITH SOLDER PROCESS

3. SILKSCREEN : WHITE EPOXY INK
A. TE LOGO, TE P/N
B. WORD REV., FOLLOWED BY THE LATEST REVISION, AS SHOWN/
C. 4 DIGITS DATE CODE : FIRST 2 DIGITS FOR THE WEEK CODE AND THE 2ND TWO DIGITS FOR THE YEAR CODE.
OTHERS : SPECIFIED TE SOURCE CODE NUMBER DIGITS AS REQUIRED.


4. CONSULTS TE CONNECTIVITY DATA SHEET L000697
5. CONTACT TE CONNECTIVITY ENGINEERING PRIOR TO DESIGNING INTO AN APPLICATION.
6. PACKAGING: SECURELY VACUUM PACKAGED IN BULK.

VACUUM IN BULK		L000697-80
PACKAGING		PART NUMBER
1	SMA FEMALE CONNECTOR	3
1	EVB	2
1	L000696-01 ANTENNA	1
Q'TY (PC)	DESCRIPTION	ITEM


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW. PARK		04JUN2024		 TE Connectivity	
		CHK S.J. NOH		04JUN2024			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		APVD Ng. WEITAT		NAME Ceramic Patch ant, 2400-2500MHz, 12x12x4	
				PRODUCT SPEC 108-160936			
				APPLICATION SPEC -		SIZE A3	
				WEIGHT -		CAGE CODE 00779	
MATERIAL SEE NOTE 1		FINISH -		DRAWING NO C-L000697		RESTRICTED TO -	
-		-		CUSTOMER DRAWING		SCALE 2:1	
						SHEET 3 OF 4	
						REV A	

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			


PACKAGING SPECIFICATIONS
FOR REFERENCE




ANTENNA WITH EVB ASS'Y




IPC/BAG
DRYING AGENT : IPC/BAG




10PCS/ZIPPER BAG




4 ZIPPER BAGS/BOX
40PCS/BOX
BOX SIZE : 154x263x96(MM)



4 BOXES



4 BOXES/CARTON
160PCS/CARTON
SIZE : 330x280x254(MM)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	DW.PARK	04JUN2024	 TE Connectivity	
		CHK	SJ.NOH	04JUN2024		
		APVD	Ng.WEITAT	04JUN2024		
		PRODUCT SPEC	108-160936			
		APPLICATION SPEC	-		NAME	
		WEIGHT	-		Ceramic Patch ant, 2400-2500MHz, 12x12x4	
		CUSTOMER DRAWING			SIZE	
					CAGE CODE	
					DRAWING NO	
					RESTRICTED TO	
					A300779	
					C=L000697	
					SCALE	
					1:1	
					SHEET	
					4 OF 4	
					REV	
					A	