


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2078410006](#)
Status: **Active**
Overview: [L1NK Connector System](#)
Description: L1NK 250 Receptacle Housing, Single Row, 6 Circuits, UL 94V-0, Black

Documents:

3D Model	Packaging Specification 2078410000-PK-000 (PDF)
Drawing (PDF)	Test Summary 2079020000-TS-000 (PDF)
Product Specification 2079020001-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 2079020001-AS-000 (PDF)	



Agency Certification

CSA	152514
UL	E29179

General

Product Family	Crimp Housings
Series	207841
Application	Power, Wire-to-Board
Datasheet Order No	987651-9951
Overview	L1NK Connector System
Product Name	L1NK 250
UPC	191130123971

Physical

Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.458/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	2079020001-AS-000
Packaging Specification	2078410000-PK-000
Product Specification	2079020001-PS-000
Sales Drawing	2078410004-SD-000
Test Summary	2079020000-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[207841](#) Series

Mates With

L1NK 250 Header [207843](#)

Use With

L1NK 250 Crimp Terminals [46626](#)

L1NK 250 TPA [207845](#)