

## CG 10-125

### Compact angle grinders, Ø 125 mm

Ergonomic 1 000 W compact angle grinder for deburring, sanding and cutting.

Product number: 7 222 79 60 00 0



### Details

- > Robust motor for daily use.
- > Compact and easy to use thanks to slim motor housing.
- > Gearbox head can be rotated 90° for high versatility.
- > Good ability to cope with overload thanks to direct motor cooling.
- > Abrasive materials can be changed at speed and without the need for any tools: quick-clamping nut included in scope of supply as standard.
- > Rapid work progress thanks to powerful motor.
- > Enhanced safety through integrated restart protection.

### Price includes

- ✓ 1 wheel guard
- ✓ 1 handle
- ✓ 1 Tool-free quick-clamping nut
- ✓ 1 key

### Product feature

- ✓ Soft start
- ✓ Restart protection

## Application

Roughing-down



Deburring



Dividing



Brushing



★ suitable  
★★ well suitable

## Technical data

### TECHNICAL DATA

Input	1,000 W
Output	630 W
Speed, no load	11,000 rpm
Grinding disc Ø	125 mm
Elast. Backing pad Ø	125 mm
Flange	M 14
Cable with plug	4 m
Weight according to EPTA	2.10 kg

### VIBRATION AND SOUND EMISSION VALUES

Sound pressure level LpA Uncertainty of measured value KpA	91 dB 3 dB
Sound power level LWA Uncertainty of measured value KWA	102 dB 3 dB
Vibration value 1 $\alpha_{hv}$ 3-way	8,5 m/s <sup>2</sup>
Vibration value 2 $\alpha_{hv}$ 3-way	3 m/s <sup>2</sup>
Uncertainty of measured value K $\alpha$	1,5 m/s <sup>2</sup>

Application examples

