

OFYS-RT-U3000

Strong points

- Fast and easy installation
- Easy to use
- Reliable power protection

General characteristics

- No configuration needed on first startup.
- 19" Rack & Rack/Tower convertible UPS.
- True online double conversion technology (VFI).
- Clear and uncluttered LCD interface.
- Up to 7 UPS output sockets.

Compliance with standards

- IEC 62040-1
- IEC 62040-2
- IEC 62040-3

Access to resources (ex: manuals)

OFYS RT is a single-phase UPS range designed to protect professional IT infrastructures, ensuring cost competitive solutions.

Technical Characteristics

Length of the product unit [mm]	89
Width of the product unit [mm]	438
Depth of the product unit [mm]	630
Weight [kg]	29.3
Depth [mm]	630
Height [mm]	89
In/out	1/1
Output voltage	230
Rated frequency	50/50
Width [mm]	438
Sn [kVA]	3
Pn [kW]	2.7
Conf	C1
Input voltage	230
Rate (min)	3
Rate (max)	3
Life Time	03-05
Typical Backup Time [min]	8
Configuration	UPS Single Unit(s) with Bypass

Classification

UNSPSC	39121011
ETIM Class	EC000382
IGCC	4149

Commerce

Description	OFYS RT 3000VA VFI UPS 1/1 PF=0,9 WITH BATTERY INTEGRATED
Effective date	2022-02-22
Offer Life Cycle Code	40

ETIM - Electrical characteristics

Input voltage [V]	180..280
Primary frequency [Hz]	40..70
Number of phases primary	1
Output voltage [V]	200..240
Secondary frequency [Hz]	50..60
Output effective power [W]	2700
Output apparent power [VA]	3000
Number of phases secondary	1
SNMP	Yes
Voltage type	AC
Max. voltage distortion output (linear load) [%]	3
Output power factor	0.9

ETIM - Mechanical characteristics

Height [mm]	89
Width [mm]	440

Depth [mm]	630
Weight [kg]	29.3
Construction type	482.6 mm (19 inch) device
Modular	No
Input connection	C20
Number of output connections C13	6
Number of output connections C19	1

ETIM - Technical features

USB interface	Yes
With communication interface RS-232	Yes
Suitable for network-management	Yes
USV- technology	Online
Overall efficiency [%]	90
Efficiency in eco-mode [%]	95
Potential free switch contact	Yes
Auto shut down function	Yes

Logistics

GTIN/EAN	8027122770408
Customs number	8504409590

Norms

Conformity to standards	IEC
-------------------------	-----