

FOC-C-LCD-MM - FO connectors




1089521

<https://www.phoenixcontact.com/in/products/1089521>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

LC duplex multimode connector for wire or cable assembly



Product description

LC duplex connector, for assembling onto wires or cables with a diameter of 2.0 mm or 3.0 mm, multimode 50/125 μm . The reusable connector is particularly suitable for quick and easy field connection, as there is no need for bonding and polishing.

Your advantages

- Suitable for quick and easy field assembly or repair
- No bonding or polishing
- Reusable connectors
- A real alternative to splicing
- Optimum attenuation values with easy assembly
- Long-term durability thanks to the latest index matching gel

Commercial data

Item number	1089521
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABN
Product key	ABNIAC
GTIN	4055626894119
Weight per piece (including packing)	9.5 g
Weight per piece (excluding packing)	9.5 g
Customs tariff number	85367000
Country of origin	DE

Technical data

Product properties

Product type	Fiber optic connector (cable side)
Type	LC
Number of positions	2
Connection profile	LC duplex plug
Number of slots	2
Type	LC
Cable outlet	straight

Electrical properties

Attenuation	≥ 0.5 dB 900 μm (95%, <0.7 dB for cable connection)
-------------	---

Connection data

Connection method	mechanical splice
-------------------	-------------------

Dimensions

Mechanical characteristics

Ferrule diameter	1.25 mm
------------------	---------

Material specifications

Material	Plastic
Ferrule material	Zirconia ceramics
Housing material	PBT

Cable/line

Cable type	Multimode fiberglass
Cable type	for all common cable types
Cable structure	STB and TB
External cable diameter	0.25 mm up to 3 mm (for the wire and cable connection) 2 mm ... 3 mm (Core assembly)
External sheath, color	beige
Wire diameter	2 mm ... 3 mm
Individual wire diameter	900 μm (for pigtails 0.9 mm, for cable connection 2 mm and 3 mm)
Tensile strength short-term/long-term	50 N
Halogen-free	yes
Flame resistance	yes

FO cable

Number of fibers	2
Fiber	Fiberglass
Fiber type	Multimode 50/125 μm

FOC-C-LCD-MM - FO connectors



1089521

<https://www.phoenixcontact.com/in/products/1089521>

Transmission medium	FO
---------------------	----

Mechanical properties

Tensile strength short-term/long-term	50 N
---------------------------------------	------

Mechanical data

Insertion/withdrawal cycles	≥ 500 (according to IEC 61300-2-2)
Extraction force per signal contact	≥ 50 N (Cable connection in accordance with IEC 61300-2-4)

Characteristics

Attenuation	≥ 0.5 dB 900 μm (95%, <0.7 dB for cable connection)
-------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C (with cable connection only at room temperature)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C

Standards and regulations

Flame resistance	yes
------------------	-----

Mounting

cable layer type	Indoors
------------------	---------

FOC-C-LCD-MM - FO connectors



1089521

<https://www.phoenixcontact.com/in/products/1089521>

Classifications

ECLASS

ECLASS-11.0	27440390
ECLASS-12.0	27440390
ECLASS-13.0	19170122

ETIM

ETIM 9.0	EC001122
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FOC-C-LCD-MM - FO connectors



1089521

<https://www.phoenixcontact.com/in/products/1089521>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

FOC-C-LCD-MM - FO connectors

1089521

<https://www.phoenixcontact.com/in/products/1089521>



Mandatory accessories

FOC-TOOL-SET-GOF - Tool set

1089515

<https://www.phoenixcontact.com/in/products/1089515>



Tool set for GOF assembly

Accessories

FOC-TOOL-FERRULECLEANER-1.25 - FO accessories

1407032

<https://www.phoenixcontact.com/in/products/1407032>



Ferrule cleaner, 1.25 mm, for LC, approx. 500 cleaning cycles

FOC-C-LCD-MM - FO connectors

1089521

<https://www.phoenixcontact.com/in/products/1089521>



FOC-OE-OE-GZ01/... - FO cable

1411561

<https://www.phoenixcontact.com/in/products/1411561>

Fiber optic cable, multi-mode fiberglass 50/125 μm , OM2, length: various



FOC-OE-OE-GZ02/... - FO cable

1411563

<https://www.phoenixcontact.com/in/products/1411563>

Fiber optic cable, multi-mode fiber glass 50/125 μm , OM3, length: various



FOC-C-LCD-MM - FO connectors

1089521

<https://www.phoenixcontact.com/in/products/1089521>




FOC-OE-OE-GZ03/... - FO cable

1411564

<https://www.phoenixcontact.com/in/products/1411564>

Fiber optic cable, multi-mode fiberglass 50/125 µm, OM4, length: various



FOC-TOOL-SET-GOF - Tool set

1089515

<https://www.phoenixcontact.com/in/products/1089515>

Tool set for GOF assembly



FOC-C-LCD-MM - FO connectors

1089521

<https://www.phoenixcontact.com/in/products/1089521>



FOC-TOOL-FERRULECLEANER-1.25 - FO accessories

1407032

<https://www.phoenixcontact.com/in/products/1407032>

Ferrule cleaner, 1.25 mm, for LC, approx. 500 cleaning cycles



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in