

1658DGTB

IP65 digital outside micrometers, reading to 0.001 mm

CE

DIN 863CE

- Reading to 0.001 mm
- Hardened steel calipers
- Lever slider locking
- Mm/inch conversion
- Zero setting at any position
- Absolute and incremental measurement modes
- Supplied with a calibration wrench

IP 65

art.	art.	A mm	G mm	L mm
016580525	1658DGTB 25	0÷25	0,001	165
016580550	1658DGTB 50	25÷50	0,001	190

