

1498/PR20

Conventional battery charger, 12/24V

CE

Semiprofessional battery chargers for lead-acid storage batteries. Designed with ultra high quality internal transformers, these devices embody the perfect balance between tradition and innovation. Based on the voltage/current selectors, built-in ammeters and automatic thermal overload and reverse polarity protectors, they ensure safe, reliable performance.

 6,1 Kg

Technical data:

- Power supply (1ph): 230 V - 50/60 Hz
- Power: 390 W
- Voltage: 12/24 V
- Maximum current: 16 A
- Charging current: 11 A
- Charging capacity: 165 Ah 15h
- Charging positions: 2



	art.	L mm	P mm	H mm
014980732	1498/PR20	260	200	175