

Datasheet

Stock No: 811-4378

# RS Pro 3 Core Unscreened Grey 3183Y Power Cable



491958  
491992  
491998  
8114378

<b>Conductor:</b>	30/0.25mm Plain Annealed Copper (Class 5 to IEC 60228)
<b>Insulation:</b>	PVC (Type TI1 to BS EN 50363)
<b>Insulation Radial Thickness:</b>	0.70mm
<b>Diameter Over Insulation:</b>	3.00mm (Nominal)
<b>No. Of Cores:</b>	3
<b>Core Colours:</b>	Blue, Brown and Green/Yellow
<b>Sheath:</b>	PVC (Type TM2 to BS EN 50363)
<b>Sheath Radial Thickness:</b>	0.90mm
<b>Overall Diameter:</b>	8.28mm (Nominal)
<b>Voltage Rating:</b>	300/500V
<b>Conductor Resistance:</b>	13.3 $\Omega$ /km @ 20°C (Nominal)
<b>Cable Weight:</b>	113.3 kg/km (Nominal)
<b>Standard:</b>	BS EN 50525-2-11
<b>Harmonisation:</b>	H05VV-F