

## har-modular shell housing 70 1Set



Image is for illustration purposes only. Please refer to product description.

Part number	02 09 500 2070 200
Specification	har-modular shell housing 70 1Set
HARTING eCatalogue	<a href="https://harting.com/02095002070200">https://harting.com/02095002070200</a>

### Identification

Category	Accessories
Series	har-modular®
Type of accessory	Shell housing

### Version

Version	Top/side entry
Strain relief	With cable tie
Locking type	Locking lever
2 parts	Yes
Separable	Yes

### Technical characteristics

Limiting temperature	-55 ... +125 °C
Degree of protection acc. to IEC 60529	IP20
Isolation group	III

### Material properties

Material (hood/housing)	Thermoplastic resin (PC) Fibre-glass reinforced
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
Length	71.12 mm
RoHS	compliant



**Pushing Performance**  
Since 1945

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Commercial data

Packaging size	1
Net weight	34.54 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140436404
eCl@ss	27440292 Connector component (accessories)
UNSPSC 24.0	39121400