



注:

1. 適合相手リセブタクル型番 172775, 172776
 2. 製品規格 No.108-5166
 3. 取付適用規格 114-5072
 4. 相手ハウジング型番 172518 他
- △ 逆巻きリール

NOTES;

1. MATE TAB P/N 172775, 172776
 2. PRODUCT SPEC. No. 108-5166
 3. APPLICATION SPEC. No. 114-5072
 4. PLUG HSG P/N 172518 ETC.
- △ REVERSE REEL

172780-1	錫メッキ済 (PRE-TIN)	黄銅 (BRASS)	△1-172779-1	4
172780-4	錫メッキ済 (PRE-TIN)	磷青銅 (PHOS BRQ)	172779-4	3
172780-2	金メッキ (SELECTIVE GOLD)	黄銅 (BRASS)	172779-2	2
172780-1	錫メッキ済 (PRE-TIN)	黄銅 (BRASS)	172779-1	1
バラ状端子型番 (P. NO.)	仕上 (FINISH)	材料 (MATERIAL)	型番 (P/N)	項番 (ID)

© 19 BY AMP (Japan) LTD.
ALL RIGHTS RESERVED.
AMP PRODUCTS COVERED BY PATENTS
AND OR PATENTS PENDING

AMP AMP (JAPAN) LTD.
Tokyo, Japan

WIRE RANGE		INSULATION DIA		NAME	
0.3~0.89 mm ² (AWG#22~#18)		1.5~2.6 mm		タブコンタクト マルチインターコネクタ (MIC) マーク II TAB MIC MK II	
MATERIAL 表参照 SEE TABLE		FINISH 表参照 SEE TABLE		GENERAL TOLERANCE	
J-10629		DR. H. Betowalla'89		0<mm<10 : ±0.2 10<mm<30 : ±0.25 30<mm<100 : ±0.3 ANGLES : ±3°	
C REDRAWN W/CHANGE		DE. H. Betowalla'89		SIZE	LOC
LTR	REVISION RECORD	DR	CHK	DATE	NUMBER
					C-172779
					SCALE 5-1
					REV. C
					SHEET 1 OF 1