

Exterior friction micrometer 1/100th mm accuracy



Standards:

NF EN ISO 3611, ISO 3611, DIN 863

Description:

- Accuracy: 1/100th - 0.01 mm.
- Accuracy: 0.01 mm.
- Carbide plunger tip: Ø 6.5 mm.
- Ratchet drum with torque limiter.
- Force applied on the part included strictly between 5 and 10 N.m.
- Drum = Ø 18 mm.
- Plunger tip lock.
- Supplied in plastic case.
- Supplied with compliance certificate.

	Weight [g]	Flatness OF Measuring Surfaces/Max ["]	Parallelism Of Measuring Faces ["]
806.F	273.0	0.4	2.0