

297152

Aluminium handle, waterfed,  
1080 - 1600 mm, Ø32 mm,  
Black



This professional telescopic water-fed handle (1060–1600 mm) has an insulated sleeve for a comfortable grip and a tapered hose connector. Maximum water pressure, 6 bars.

# Technical Data

<b>Item Number</b>	297152
<b>Material</b>	Anodised Aluminium Polypropylene Chromium-plated brass
<b>Meets the REACH Regulation (EC) No. 1907/2006</b>	Yes **
<b>Box Quantity</b>	5 Pcs.
<b>Quantity per Pallet (80 x 120 x 200 cm)</b>	580 Pcs.
<b>Quantity Per Layer (Pallet)</b>	25 Pcs.
<b>Box Length</b>	1110 mm
<b>Box Width</b>	140 mm
<b>Box Height</b>	85 mm
<b>Product Diameter</b>	32 mm
<b>Length/Depth</b>	1080 mm
<b>Width</b>	32 mm
<b>Height</b>	32 mm
<b>Max. Length</b>	1600 mm
<b>Gross Weight</b>	0,7 kg
<b>Net Weight</b>	0,64 kg
<b>Cubik metre</b>	0,0011 M3
<b>Max. bars pressure</b>	6 Bar
<b>Max usage temperature (non food contact)</b>	50 °C
<b>Min. pH-value in usage concentration</b>	4 pH
<b>Max. pH-value in Usage Concentration</b>	11 pH
<b>GTIN-13 Number</b>	5705022971011
<b>GTIN-14 Number (Box quantity)</b>	15705022971018
<b>Commodity Code</b>	76082020
<b>Country of origin</b>	Denmark

\*\* Lead (Pb, CAS: 7439-92-1) is on the REACH candidate list as a Substance of Very High Concern (SVHC). This product contains lead (Pb) in a concentration above 0.1% w/w. Consequently the REACH Regulation (EC) No. 1907/2006 require Vikan to notify our customers of the content of lead.