



PW3 HI-VIS WORK TROUSERS

DESCRIPTION

Constructed using premium HiVisTex Pro tape and durable polyester/cotton fabric, this contemporary Hi-Vis Work Trousers provides ultimate wearer comfort. Oxford fabric reinforcement at key abrasion points and triple stitching throughout guarantees maximum durability. This trouser features top loading kneepad pockets and an easy access multiway thigh pocket for secure storage of your phone, keys and tools.

COMPOSITION

-  **Titanmill Plus: 65% Polyester, 35% Cotton, 300g**
-  **100% Polyester, 600D Oxford, PU Coated, 210g**
-  **Yellow/ Navy 28-48**

FEATURES

- Durable polycotton fabric with Texpel stain resistant finish
- Texpel™ Stain Eco a premium stain resistant finish to repel grime and water
- High rise back waistband ensures protection in all working positions
- Easy access cargo pocket
- Extendable leg length (31" to 33")
- Free pair of kneepads included with this trouser
- Triple-stitched seams for extra durability
- 2 Side pockets
- Two back patch pockets
- Double rule pocket
- D-ring for keys or ID cards
- Hammer loop for secure storage of work tools

STANDARDS

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)
ANSI/ISEA 107 SUPPLEMENTAL CLASS E

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
PW340YNR	YELLOW/NAVY	28-14

FEATURES



TOP-LOADING KNEE PAD POCKETS
Top-loading knee pad pockets for quick and easy access



HALF ELASTICATED WAIST
Half elasticated waist for a secure and comfortable fit



HEAT APPLIED SEGMENTED REFLECTIVE TAPE
This symbol indicates that the garment has heat applied reflective tape



STANDARDS



EN ISO 20471
High Visibility Clothing - Test Methods
And Requirements



PERFORMANCE WORKWEAR
PW3™ contemporary workwear blends
sports and lifestyle trends with function,
a modern fit and improved comfort.

GET THE
COLLECTION



TECHINCAL INFORMATION



SATRA Technology Europe Ltd
(Notified Body Number.: NB: 2777) Bracetown
Business Park Clonee Dublin 15 D15 YN2P, Ireland
Cert No: 2777/14048-03/E00-00

· Wash garment inside out and fully
fastened

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
PW340YNR28	Yellow/Navy	65	45	36	.960	5850.000	5036108307685	15036108796769
PW340YNR30	Yellow/Navy	65	45	36	.986	5850.000	5036108307692	15036108796776
PW340YNR32	Yellow/Navy	65	45	36	.996	5850.000	5036108307708	15036108796783
PW340YNR33	Yellow/Navy	65	45	36	1.016	5850.000	5036108307715	15036108796790
PW340YNR34	Yellow/Navy	65	45	36	1.010	5850.000	5036108307722	15036108796806
PW340YNR36	Yellow/Navy	65	45	36	1.050	5850.000	5036108307739	15036108796813
PW340YNR38	Yellow/Navy	65	45	36	1.070	5850.000	5036108307746	15036108796820
PW340YNR40	Yellow/Navy	65	45	36	1.060	5850.000	5036108307753	15036108796837
PW340YNR41	Yellow/Navy	65	45	36	1.080	5850.000	5036108307760	15036108796844
PW340YNR42	Yellow/Navy	65	45	36	1.100	5850.000	5036108307777	15036108796851
PW340YNR44	Yellow/Navy	65	45	36	1.080	5850.000	5036108307784	15036108796868
PW340YNR46	Yellow/Navy	65	45	36	1.100	5850.000	5036108307791	15036108796875
PW340YNR48	Yellow/Navy	65	45	36	1.140	5850.000	5036108307807	15036108796882