



- △ MATERIAL: CONNECTOR-NYLON UL94V-2 (RED). CONTACTS-0.30 [.012] THICK COPPER ALLOY 0.00038 [.000015] GOLD IN CONTACT AREA WITH BRIGHT TIN-LEAD FOR 641190-2 THRU 2-641190-8, MATTE WHISKER MITIGATED TIN FOR 3-641190-2 THRU 5-641190-8 OVER NICKEL UNDERPLATE.
- CONTACTS ACCEPT 22 AWG WIRE WITH 1.52 [.060] MAX INSULATION DIAMETER.
 - CONTACTS MUST ACCEPT 0.64±0.03 [.025±.001] SQUARE POST AND REMAIN LOCKED IN POSITION.
- △ IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
- DIMENSIONS IN BRACKETS ARE IN INCHES.
 - HOUSING FEATURES ARE: CLOSED END WITH LOCKING RAMP.
 - OBsolete PARTS: OBsolete CIS STREAMLINING PER D.RENAUD/D.SINISI

71.12	[2.800]	28	5-641190-8
66.04	[2.600]	27	5-641190-7
63.50	[2.500]	26	5-641190-6
63.50	[2.500]	25	5-641190-5
60.96	[2.400]	24	5-641190-4
58.42	[2.300]	23	5-641190-3
55.88	[2.200]	22	5-641190-2
53.34	[2.100]	21	5-641190-1
50.80	[2.000]	20	5-641190-0
48.26	[1.900]	19	4-641190-9
45.72	[1.800]	18	4-641190-8
43.18	[1.700]	17	4-641190-7
40.64	[1.600]	16	4-641190-6
38.10	[1.500]	15	4-641190-5
35.56	[1.400]	14	4-641190-4
33.02	[1.300]	13	4-641190-3
30.48	[1.200]	12	4-641190-2
27.94	[1.100]	11	4-641190-1
25.40	[1.000]	10	4-641190-0
22.86	[.900]	9	3-641190-9
20.32	[.800]	8	3-641190-8
17.78	[.700]	7	3-641190-7
15.24	[.600]	6	3-641190-6
12.70	[.500]	5	3-641190-5
10.16	[.400]	4	3-641190-4
7.62	[.300]	3	3-641190-3
5.08	[.200]	2	3-641190-2
DIM A		NO.OF POSN	ASSEMBLY

71.12	[2.800]	28	2-641190-8
66.04	[2.600]	27	2-641190-7 △
63.50	[2.500]	26	2-641190-6 △
63.50	[2.500]	25	2-641190-5 △
60.96	[2.400]	24	2-641190-4 △
58.42	[2.300]	23	2-641190-3
55.88	[2.200]	22	2-641190-2 △
53.34	[2.100]	21	2-641190-1 △
50.80	[2.000]	20	2-641190-0
48.26	[1.900]	19	1-641190-9 △
45.72	[1.800]	18	1-641190-8
43.18	[1.700]	17	1-641190-7 △
40.64	[1.600]	16	1-641190-6
38.10	[1.500]	15	1-641190-5
35.56	[1.400]	14	1-641190-4
33.02	[1.300]	13	1-641190-3
30.48	[1.200]	12	1-641190-2
27.94	[1.100]	11	1-641190-1
25.40	[1.000]	10	1-641190-0
22.86	[.900]	9	641190-9
20.32	[.800]	8	641190-8
17.78	[.700]	7	641190-7
15.24	[.600]	6	641190-6
12.70	[.500]	5	641190-5
10.16	[.400]	4	641190-4
7.62	[.300]	3	641190-3
5.08	[.200]	2	641190-2
DIM A		NO.OF POSN	ASSEMBLY



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN S. HOOVER 20-DEC-2004	APVD D. ROSSI 20-DEC-2004	NAME
0. PLC ±	±			MTA .100 CONNECTOR ASSEMBLY
1. PLC ±	±			22 AWG, STANDARD
2. PLC ±	±			
3. PLC ±	±			
4. PLC ±	±			
ANGLES ±	±			
MATERIAL	FINISH	SIZE	CAGE CODE	DRAWING NO
		A1	00779	641190
		WEIGHT	SCALE	SHEET
			5:1	1 OF 1
		CUSTOMER DRAWING	REV	K2