

10m Coax High Resolution Monitor VGA Video Extension Cable - HD15 M/F

Product ID: MXTHQ10M



The MXTHQ10M High Resolution VGA Extension Cable (10-meter) is designed to extend your VGA video connection while maintaining the highest video quality possible through VGA.

Ideally suited for high resolution VGA video applications, this high quality coaxial VGA extension cable (HD15 to HD15, M-F) helps eliminate the picture ghosting and fuzzy images that are inherent to non-coaxial cables, and features ferrite cores near the VGA connector ends to protect against EMI interference.

Certifications, Reports and Compatibility



Applications

- Extend your SVGA/VGA cable, for more convenient monitor placement
- Extend the connection distance between monitors, video splitters, projectors and a VGA video source

Features

- Triple coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief
- Ferrite cores to help eliminate EMI interference

Connector(s)	Warranty	Lifetime
	Connector A	1 - VGA (15 pin, High Density D-Sub) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female
Physical Characteristics	Cable Length	10 m [32.8 ft]
	Color	Black
	Product Length	10000 mm [393.7 in]
	Product Weight	1 kg [2.1 lb]
	Wire Gauge	28 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	1 kg [2.2 lb]
What's in the Box	Included in Package	1 - 10m Coax High Resolution VGA Monitor Extension Cable - HD15 M/F
		2 - Nuts

Product appearance and specifications are subject to change without notice.