



PRODUCT-DETAILS

MLBL-00BG

MLBL-00BG LED block



360°

概要信息	
产品型号	MLBL-00BG
产品ID	1SFA611621R2002
欧洲商品编号(EAN)	7320500545072
目录说明	MLBL-00BG LED block
详细描述	The MLBL-00BG LED block is: Without holder - Green - Illuminated - Rear mounting - 12 V This LED block is part of ABB's modular plastic range, the most versatile range with a high level of flexibility and market-leading electrical ratings. Engineered for total reliability, longer lifetime, and highest mechanical durability. Self-cleaning contacts ensure reliable operation without the need for maintenance, increasing uptime. A high degree of protection guarantees reliability in extreme environments. The innovative design simplifies the entire process, from selection to easy and quick, tool-free installation. The perfect solution for every application.

订货信息	
最小起订量	10 piece
海关关税号	85369001

Popular Downloads	
数据手册，技术资料	1SFC151007C02__
说明书和手册	1SFC151011M0201

尺寸	
产品净宽	0.01 m
产品净高	0.044 m
产品净深	0.042 m
产品净重	0.01 kg

技术参数	
周围环境温度	Operation -25 ... +70 °C Storage -40 ... +85 °C
颜色	Green
照明	Illuminated
灯类型	12V DC, integrated LED
安装类型	Rear mounting
额定工作电压	12 V DC
连接容量	Flexible with Ferrule 1 x 0.75...2.5 mm ² Flexible with Ferrule 2 x 0.75...2.5 mm ² Flexible with Insulated Ferrule 1 x 0.75...2.5 mm ² Flexible with Insulated Ferrule 2 x 0.75...2.5 mm ² Flexible 1 x 0.75 ... 2.5 mm ² Flexible 2 x 0.75 ... 2.5 mm ² Solid 1 x 0.75...2.5 mm ² Solid 2 x 0.75...2.5 mm ²
连接类型	Screw Clamp
端子类型	Screw Terminals
拧紧力矩	0.9 N·m
剥线长度	8 mm
适用于	MCBH-00 MCBH5-00 MP1 MP2 MP3 MP4 MPMT3 MPMP3 M2SS1 M2SS2 M2SS3 M2SS4 M2SS5 M2SS6 M3SS1 M3SS2 M3SS3 M3SS4 M3SS5 M3SS6 M3SS7 M3SS8 MPM1
适用产品系列	Pilot Devices

UL/CSA适用的技术参数	
---------------	--

连接容量UL/CSA	1x 18...14 AWG
	2x 18...14 AWG

环境条件

防护等级	Terminals IP20
------	----------------

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2022-006479
RoHS信息	2CMT2022-006498
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006523
WEEE B2C / B2B	Business To Business
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

认证及声明（文件编码）

CB认证	SEMKO_SE-56219
CQC认证	CQC2008010305274953
cULus 认证	9AKK107046A9925
Declaration of Conformity - CCC	2020980305001106
符合性声明 - CE	2CMT2015-005452
Declaration of Conformity - UKCA	2CMT2020-006121
DNV GL Certificate	E-14107
EAC认证	1SFC150017D1101

包装信息

1级包装单元	bag 10 piece
1级包装宽度	0.135 m
1级包装长度	0.155 m
1级包装高度	0.025 m
1级包装 总重	0.11 kg
1级包装 EAN	7320500373675

分类

对象分类代码	E
ETIM 6	EC000204 - Lamp holder block for control circuit devices
ETIM 7	EC000204 - Lamp holder block for control circuit devices
ETIM 8	EC000204 - Lamp holder block for control circuit devices
e级	V11.0 : 27371209
UNSPSC	39122221
IDEA 粒度分类代码 (IGCC)	5219 >> Switch part or accessory
E-Number (Finland)	2315791

分类

低压产品及系统 → 控制产品 → 按钮指示装置 → Accessories
低压产品及系统 → 控制产品 → 按钮指示装置 → 按钮和指示灯

