NT 30/1 TACT TE H

With a guaranteed filtration efficiency of 99.995%, the 30/1 Tact Te H wet and dry vacuum cleaner is the first choice for removing dusts hazardous to health in dust class H.

Made in Europe

Order no.	1.148-257.0

- Complete antistatic system, incl. conductive accessories
- Socket with automatic start-up for electric tools
- Licensed for asbestos abatement

Technical data		
EAN code		4054278483672
Current type	Ph / V / Hz	1 / 220 - 240 / 50 - 60
Air flow	l/s	74
Vacuum	mbar / kPa	273 / 27.3
Container content	l	30
Rated input power	W	max. 1380
Standard nominal width		ID 35
Cable length	m	7.5
Sound pressure level	dB(A)	69
Colour		anthracite
Weight without accessories	kg	14.4
Weight incl. packaging	kg	19.6
Dimensions (L × W × H)	mm	560 × 370 × 580

Equipment		
Safety filter bag	Piece(s)	1
Suction hose length	m	4
Suction hose type		electrically conductive
Quantity of suction tubes	Piece(s)	2
Suction tubes length	mm	550
Suction tubes material		Stainless steel
Bend		electrically conductive
Filter bag material		Fleece
Wet/dry floor nozzle width	mm	360
Crevice nozzle		■
Connector for electric tools		■
Automatic on/off control for electric power tools		■
Antistatic system		■
Flat pleated filter		PTFE HEPA
Sturdy bumper		■
Safety class		I
Caster with brake		■
Filter cleaning		Tact - Auto Filter Clean System
PE-Plastic bag for dust-free disposal	Piece(s)	1
Container material		Plastic

■ Included in delivery.

NT 30/1 TACT TE H, 1.148-257.0, 2025-03-14

Filtration system with H filter and Tact filter cleaning system

- Sucks less dangerous dust directly into the container. Filtration efficiency: 99.995 per cent.
- The greatest possible health protection without sacrificing suction power or filter endurance.

Fulfils testing requirements for dust class H, with additional test for "Asbestos" in accordance with TRGS 519

- In Germany, only safety vacuum cleaners with this licence are allowed to be used to vacuum dust that contains asbestos.



Complete antistatic system with conductive accessories

NT 30/1 TACT TE H, 1.148-257.0, 2025-03-14

KÄRCHER

EQUIPMENT FOR NT 30/1 TACT TE H
1.148-257.0

1

2


3


4

5

6

7

8

9


10

11

12


13

14

		Order no.	Description	
FILTER T/ NT				
Flat pleated filter HEPA, dust class H				
Flat pleated filter, PTFE H class	1	6.907-671.0	HEPA flat pleated filter made from PTFE. Suitable for dust class H (HEPA 13).	■
HEPA surface filter	2	6.904-242.0	HEPA surface filter – dust class H (HEPA 13) – with glass-fibre layers increases filter capacity when vacuuming health-endangering and carcinogenic dust.	☐
Plastic sacks for dust-free disposal				
Plastic bag for dust-free disposal, 10 Piece(s), NT 30/1, NT 40/1, NT 50/1	3	2.889-158.0	PE plastic sack for dust-free disposal.	☐
	4	2.889-231.0	PU plastic bag for dust-free disposal. Pack of 10.	☐
Safety filter sets / sacks				
Safety filter bag, 5 Piece(s), NT 30/1	5	2.889-183.0	Safety filter set with dust disposal bag, for dust class H safety vacuum cleaners. Guarantees the dust-free disposal of dangerous dust.	☐
BENDS				
Plastic bend				
Elbow complete packaged NW35 2K	6	2.889-168.0	Ergonomic bend for the new clip system. Electrically conductive design. Particularly suited to high concentrations of fine dust.	■
Elbow packaged NW35 2K	7	2.889-170.0	Ergonomic bend for the new clip system.	☐
SUCTION NOZZLES				
All-purpose nozzles (wet/dry)				
Floor tool packaged NW35 360mm	8	2.889-152.0	360 mm wide wet and dry floor nozzle with easy-to-change inserts. Including brush strips and squeegees.	■
Floor tool anthracite packaged NW35	9	2.889-173.0	300 millimetre width, anthracite coloured wet/dry floor nozzle, NW 35. With easy-to-change inserts. Incl. brush strips and squeegees.	☐
Crevice nozzles				
Crevice nozzle wet and dry packaged NW35	10	2.889-159.0	Crevice nozzle ID 35, for new Tact range.	■
Car cleaning nozzles				
Car nozzle, ID 35, 90 mm	11	6.906-108.0	Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.	☐
SUCTION TUBES				
Suction tubes stainless steel				
Set suction tube stainless steel NW35 55	12	2.889-192.0	Stainless steel suction tube set (2 × 0.55 m)	■
Suction tubes metal				
Set suction tube chromed NW35 550mm	13	2.889-191.0	Suction tube set, metal-chrome-plated, NW 35, 2-part, each 0.55 millimetres.	☐
SUCTION HOSES				
Suction hoses with clip system 2.0 (compatible with vacuum cleaners from model year 2017 on)				
Electrically conductive suction hose	14	2.889-137.0	4 m suction hose with new bayonet and clip fastener. Electrically conductive.	■

■ Included in delivery. ☐ Available accessories.

KÄRCHER

EQUIPMENT FOR NT 30/1 TACT TE H
1.148-257.0

15

16

17

18

19

20

21

22

23

24

25

26

27

28

		Order no.	Description	
SUCTION HOSES				
Suction hoses with clip system 2.0 (compatible with vacuum cleaners from model year 2017 on)				
Suction hose	15	2.889-135.0	4 m suction hose with new bayonet and clip fastener.	☐
Electrically conductive suction hose	16	2.889-136.0	Electrically conductive suction hose with new bayonet and clip fastener. Length: 2.5 m.	☐
Suction hose	17	2.889-138.0	4 m suction hose with new bayonet and clip fastener.	☐
	18	2.889-139.0	Suction hose with new bayonet and clip fastener. Length: 2.5 m.	☐
Suction hose, oil-resistant	19	2.889-140.0	Oil-resistant suction hose with new bayonet and clip fastener. Length: 4 m.	☐
Electrically conductive suction hose	20	2.889-141.0	4 m, electrically conductive suction hose with new bayonet and clip fastener.	☐
	21	2.889-142.0	Suction hose, electrically conductive, with new bayonet and clip fastener. 2.5 m long.	☐
Extension hose packaged NW35 2.5m	22	2.889-145.0	Extension hose for new clip system ID 35. Length: 2.5 m.	☐
Repair set NW35	23	2.889-149.0	Repair kit ID 35 for the new clip system.	☐
Extension hose conductive packaged NW35	24	2.889-343.0		☐
CONNECTING SLEEVES				
Adapter for electric power tools, clip on, el.				
Sleeve electrically conducting packaged	25	2.889-151.0	Tool adaptor with a rubber fixture and airflow control slide for the new clip system. Suitable for all current electric tools.	■
Connecting sleeve C-DN (clip on taper), EL (electroconductive)				
Connection cone NW35	26	5.407-005.0		☐
OTHER ACCESSORIES FOR T AND NT				
Drilling dust tool	27	2.679-000.0	Drilling dust nozzle for dust-free vacuuming. Suitable for dry and wet and dry vacuum cleaners from Kärcher.	☐
Adapter old packaged NW35	28	2.889-312.0		☐

■ Included in delivery. ☐ Available accessories.

EQUIPMENT FOR NT 30/1 TACT TE H
1.148-257.0

29

		Order no.	Description	
OTHER ACCESSORIES FOR T AND NT				
Adapter connection old elektr. leitend	29	5.031-436.0		☐

■ Included in delivery. ☐ Available accessories.