



 **FABRIQUE EN
FRANCE**

PROFESSIONAL **5** YEARS MANUFACTURER GUARANTEE 

Product number 9150321124
EAN 3281850211243

TECHNICAL DATA

Cable quality	Rubber-Neoprene	Number of poles (FI)	4
Cable length	2 m	CEE 400 V / 16 A / 3P+N+PE (5p) Steckdosen	2
Cable designation	H07RN-F 5G4,0	CEE 400 V / 32 A / 3P+N+PE (5p) Steckdosen	1
Cable colour	black	Earthed socket outlets	4
Max. current carrying capacity	32 A	Plug system socket	Type E (FR)
Miniature circuit breaker	7	Supply/ connection option	Supply cable with plug
Residual current circuit breaker (RCCB)	FI with IFN 0.3 A	Plug system plug	CEE 32 A 3P+N+E (5p) 400 V
Rated current (FI)	30 mA	Degree of protection (IP)	IP44

PACKAGING, DIMENSIONS AND WEIGHTS

Packaging	Coloured sales box	Dimension LxWxH (without packing)	57 cm x 31 cm x 31 cm
UP	1	Weight of product (including packaging)	8.33 kg
Weight of product (without packaging)	7.62 kg	Dimension LxWxH (incl. packing)	59 cm x 32 cm x 32 cm