






REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	13APR2026	H.O	T.S
	B	REVISED	27MAY2026	H.O	T.S


1. MATERIAL:HOUSING:GLASS FILED THRMO PLASTIC(94V-0)
COLOR:SEE TABLE
CONTACT/SOLDER PEG:COPPER ALLOY
2. FINISH:ALL OVER:NICKEL PLATING 1.27umMIN
CONTACT AREA:GOLD PLATING 0.2umMIN AFTER Ni PLT.
SOLDER PEG AND CONTACT TAIL:TIN PLATING 2umMIN AFTER Ni PLT.
3. CIRCUIT NUMBER IS CONSISTED ROW ID AND CIRCUIT ID:REFER TO SHEET 7
4. RECOMMENDED PC BOARD PATTERN:REFER TO SHEET 6




1-2498846-2
X-KEY 2POSN










BLACK	Y	8	2-2498846-8
	X		1-2498846-8
BLACK	Y	6	2-2498846-6
	X		1-2498846-6
BLACK	Y	4	2-2498846-4
	X		1-2498846-4
BLACK	Y	3	2-2498846-3
	X		1-2498846-3
BLACK	Y	2	2-2498846-2
	X		1-2498846-2
COLOR	KEYING	POSN	PART NUMBER




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 13APR2026	TE Connectivity			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.5, ± 0.3° 0 PLC ± 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±	CHK T.SHIMOYASU 13APR2026				
		APVD T.SHIMOYASU 13APR2026	NAME HDR V ASSY Au TYPE D1000 SLIM, DYNAMIC -			
	PRODUCT SPEC 108-140257					
	APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO -	
	MATERIAL - -	FINISH - -	WEIGHT -	A3		00779
CUSTOMER DRAWING			SCALE	SHEET	OF	REV
			4:1	1	7	B

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



1-2498846-3
X-KEY 3POSN



2-2498846-3
Y-KEY 3POSN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 13APR2026	TE Connectivity							
		CHK T.SHIMOYASU 13APR2026								
DIMENSIONS: mm		APVD T.SHIMOYASU 13APR2026	NAME HDR V ASSY Au TYPE D1000 SLIM, DYNAMIC -							
		PRODUCT SPEC 108-140257								
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.5, ±0.3°		APPLICATION SPEC -	SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
MATERIAL - -		FINISH - -	WEIGHT -		A3		00779		C-2498846	
CUSTOMER DRAWING			SCALE		SHEET		2 OF 7		REV B	

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

KEYING

CAVITY MARK

CAMPANY LOGO


ROW ID

CIRCUIT ID

1-2498846-4
X-KEY 4POSN

2-2498846-4
Y-KEY 4POSN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE	13APR2026	 TE Connectivity	
		CHK T.SHIMOYASU	13APR2026		
		APVD T.SHIMOYASU	13APR2026	NAME HDR V ASSY Au TYPE D1000 SLIM, DYNAMIC	
		PRODUCT SPEC 108-140257			
		APPLICATION SPEC -			
		WEIGHT -		SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-2498846	RESTRICTED TO -
				SCALE 4:1	SHEET 3 OF 7
					REV B








DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.5, ± 0.3°
	0 PLC ± 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±
MATERIAL -	FINISH -

13APR2026
13APR2026
13APR2026
108-140257
-
-
CUSTOMER DRAWING

NAME HDR V ASSY Au TYPE D1000 SLIM, DYNAMIC		RESTRICTED TO -	
SIZE A3	CAGE CODE 00779	DRAWING NO C-2498846	REV B

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 13APR2026	 TE Connectivity		
		CHK T.SHIMOYASU 13APR2026			
		APVD T.SHIMOYASU 13APR2026	NAME HDR V ASSY Au TYPE D1000 SLIM, DYNAMIC		
		PRODUCT SPEC 108-140257			
		APPLICATION SPEC -	SIZE A3		
		WEIGHT -			
		CUSTOMER DRAWING	SCALE 4:1		
			SHEET 4 OF 7		
			REV B		

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

KEYING
CIRCUIT ID

CAVITY MARK

CAMPANY LOGO

ROW ID



2-2498846-8
Y-KEY 8POSN

1-2498846-8
X-KEY 8POSN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE	13APR2026	 TE Connectivity	
		CHK T.SHIMOYASU	13APR2026		
		APVD T.SHIMOYASU	13APR2026	NAME HDR V ASSY Au TYPE DI000 SLIM, DYNAMIC	
		PRODUCT SPEC 108-140257			
		APPLICATION SPEC -		SIZE A3	
		WEIGHT -			
		CUSTOMER DRAWING		SCALE 4:1	SHEET 5 OF 7
					REV B

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.5, ± 0.3°	
		0-PLC	±
		1-PLC	±0.1
		2-PLC	±0.01
		3-PLC	±0.001
		4-PLC	±0.0001
MATERIAL -		FINISH -	

D

D

C

C


B

B


A

A


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




X-2498846-2:2POSN




X-2498846-3:3POSN



X-2498846-4:4POSN




X-2498846-6:6POSN




X-2498846-8:8POSN

RECOMMENDED PC BOARD HOLE PATTERN


:CONNECTOR MOUNT SIDE(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS:1.0-1.6±0.1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 13APR2026	 TE Connectivity		
DIMENSIONS: mm		CHK T.SHIMOYASU 13APR2026			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.5, ± 0.3°		APVD T.SHIMOYASU 13APR2026	NAME HDR V ASSY Au TYPE D1000 SLIM, DYNAMIC		
		PRODUCT SPEC 108-140257	SIZE A300779		
MATERIAL -		APPLICATION SPEC -	CAGE CODE C-2498846		
FINISH -		WEIGHT -	RESTRICTED TO -		
CUSTOMER DRAWING		SCALE 4:1	SHEET 6 OF 7		REV B


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




X-2498846-2:2POSN




X-2498846-3:3POSN



X-2498846-4:4POSN




X-2498846-6:6POSN



X-2498846-8:8POSN

CURCUIT NUMBER REFERENCE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 13APR2026	TE Connectivity				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.5, ±0.3° 0 PLC ±- 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±-	CHK T.SHIMOYASU 13APR2026					
		APVD T.SHIMOYASU 13APR2026					
		PRODUCT SPEC 108-140257	NAME HDR V ASSY Au TYPE D1000 SLIM, DYNAMIC -				
		APPLICATION SPEC -					
MATERIAL - -		FINISH - -	WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2498846	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 4:1	SHEET 7 OF 7	REV B	