

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-849

Extra protection for longer period of wear



Multi Purpose Ergonomic Protection



Light Duty

## Durable, comfortable industrial gloves with fully dipped nitrile coating, for 360° coverage

- **Heightened defenses:** HyFlex® 11-849 safety gloves' fully dipped design ensures 360° protection from light scratches and dirt
- **Improved durability:** Their FORTIX™ Abrasion Resistance nitrile foam coating guarantees ANSI/EN-compliant abrasion resistance
- **Enhanced grip:** HyFlex® 11-849 safety gloves come with 2x more grip, for better performance in dry or slightly oily conditions
- **Reduced contaminants:** HyFlex® 11-849 industrial working gloves are silicone-free, avoiding contaminant transfer to metal before painting
- **Certified harm-free:** Dermatest® and Oeko-Tex® certification ensure these PPE gloves are skin-friendly and free of harmful substances
- **Elevated comfort:** These HyFlex® gloves' Spandex® and nylon liner is shaped to natural hand contours

### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Transportation
- Automotive Aftermarket

### Applications

- Picking, fastening components
- Fastening components, parts
- Transport & Logistics
- General handling
- Occasional handling of hot objects : EN407 Contact Heat class 1 (100°C for 15s)



# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-849

Extra protection for longer period of wear

### Key Features

- Fully dipped coating: Industrial gloves with 360° hand protection
- FORTIX™ Abrasion Resistance: 2x more grip, up to 20% more durability
- Silicone-free: No contaminant transfer to metal prior to painting

### Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Technologies



### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-849	<b>Finishing:</b> Fully Coated <b>Coating Material:</b> Foam Nitrile <b>Liner Material:</b> Spandex, Nylon <b>Cuff Style:</b> Knitwrist	18	6, 7, 8, 9, 10, 11	210-255 mm, 8.3-10 inches	Black	12 pairs/bag, 12 bags/carton

### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell®, and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

