



fitted with

work equipment
connected load
power consumption
system of protection
class of protection
technology
usage
luminaire body
lamp cover
tubular sections

balance of articulation joints
weight (net)
mains lead

fastening
lens; dimensions
lens material
lens; diopters
add-on lens; dimensions
add-on lens; diopters
special features

48 x Light-emitting diode
 light colour neutral white
 electronic plug-in ballast
 100-240 V; 50/60 Hz
 approx. 14 W
 IP 20
 II
 multi-stage switchable, continuously dimmable
 multi-function switch
 plastic, untreated, black
 screen, milky, Polyamide
 tubular aluminium section, anodized, aluminium coloured
 anodised
 spring
 approx. 2.7 kg
 approx. 3.4 m; mains plug
 BS 1363
 CEE 7/XVI
 NEMA 1-15P
 screw-down flange
 Ø 160 mm
 glass
 3,5
 Ø 31.5 mm
 8
 adhesive add-on magnifier, long arms, light characteristic
 can be adjusted with a three-way switch



BS 1363



CEE 7/XVI



NEMA 1-15P

illuminance

Comment: d=15cm

Em: 4002 lx
 Emax: 6141 lx
 Emin: 1377 lx

