

PREVOST FILTRATION - UNIT COMBINATIONS

Lubricator filter-regulator - 3 units



Part number	Female thread	Flow rate at 6.00 bar (l/min) ($\Delta P = 1.00$ bar)	Max. operating pressure (bar)	Filtration (μm)	Net weight (Kg)
ATU T2510100	G1/8	500.00	10.00	25.00	0,977
ATU T2510101	G1/4	800.00	10.00	25.00	0,977
ATU T2510102	G3/8	2200.00	10.00	25.00	2,446
ATU T2510103	G1/2	3500.00	10.00	25.00	2,446

