

Data sheet

Commercial Art.No.: 76.320.0753.0

bottom MIN GUT GA 7 25 P

Bottom-base revos MINI made of Plastik, ankled, open, low version



Technical data

general

housing material	plastic
color	white
surface	untreated
degree of protection (IP)	IP54
UV resistant	yes
flammability class of insulation material acc. with UL94	V0
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	3
model of the housing	equipment mounted (feed-through)
locking mechanism	single locking lever
cable entry	none
type of cable	none
with cable screw gland	no
thread size PG	
hinged lid	no
EMC-version	no
length	40 mm
width	36.5 mm
height	23 mm

classification

ECLASS 11	
ECLASS 8.1	27440202
ETIM 9.0	EC000437
ETIM 8.0	EC000437

ETIM 7.0	EC000437
ETIM 6.0	EC000437
ETIM 5.0	EC000437
ETIM 4.0	EC000437
ETIM 3.0	EC000437

product compliance

ROHS conformity status	compliant
REACH-SVHC conformity status	compliant