

Easy9 Residual Current Circuit Breaker - 2P - 63 A - 30 mA - A type - 230 V

EZ9R46263

EAN Code: 3606481275769

Main

Range of product	Easy9	
Product or component type	Residual current circuit breaker (RCCB)	
Device short name	Easy9 RCCB	
Poles	2P	
Neutral position	Left	
[In] rated current	63 A	
[In] rated current	63 A	
Network type	AC	
Earth-leakage sensitivity	30 mA	
Earth-leakage protection time delay	Instantaneous	
Earth-leakage protection class	Type A	
Rated breaking and making capacity	500 A	
Rated conditional short-circuit current	Easy9 MCB: 6000 A 63 A	

Complementary

Device location in system	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	230 V AC 50/60 Hz
[Ui] rated insulation voltage	440 V AC
[Uimp] rated impulse withstand voltage	4 kV
Contact position indicator	Yes
control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top: YES
Connection pitch	18 mm between phases
9 mm pitches	4
Height	82 mm
Width	36 mm
Depth	72 mm

Colour	Grey (RAL 7035)	
Mechanical durability	5000 cycles	
Electrical durability	AC: 2000 cycles 230 V AC 50 Hz	
Connections - terminals	Tunnel type terminal (top or bottom) 135 mm² rigid Tunnel type terminal (top or bottom) 125 mm² flexible	
Wire stripping length	16 mm for top or bottom connection	
Tightening torque	3.5 N.m top or bottom	

Environment

Standards	IEC 61008-1
Product certifications	CE
IP degree of protection	IP20
Pollution degree	2 conforming to IEC 61008-1
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-560 °C
Ambient air temperature for storage	-4085 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	4 cm
Package 1 Length	9 cm
Package 1 Weight	250 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	9.2 cm
Package 2 Width	9.7 cm
Package 2 Length	25.5 cm
Package 2 Weight	1.5 kg
Unit Type of Package 3	S03
Number of Units in Package 3	54
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	18 kg

Logistical informations

Country of origin

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	141
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	C80aa611-4852-4a2c-b49a-fd0fbf96bfd7
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No