

3U 19" Wall Mount Vertical Rack Bracket, Wall Mount Patch Panel Bracket for Data/AV/IT/Computer Equipment, 3U Rack for Cabinet or Server Room, Supports 150lb (68kg) Capacity - TAA

Product ID: RK319WALLV



This 3U 19 in server room rack enables vertical mounting of rack-mounted equipment of any depth. Mount the bracket to a wood stud wall and position equipment vertically, maximizing space utilization and optimizing layout design. The open-frame design allows for unrestricted airflow to the mounted equipment, improving cooling.

Mount the bracket into a wall featuring wood stud construction, where studs are spaced 16in (40.6cm) apart. The patch panel wall mount rack is perfect for SoHo (small office, home office) and other small footprint applications allowing you to vertically mount up to 150lb (68kg) of standard rack equipment into this 14-gauge steel bracket. The mounting holes are positioned 16in (40.6cm) apart, matching the standard for construction framework.

The vertical wall mount network rack conveniently includes 6x wood screws, 12x M5 square cage nuts, and 12x M5 screws to attach the rack to a wall and mount your equipment.

The wall mount vertical rack is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

Features

- **3U VERTICAL WALL MOUNT RACK BRACKET:** This patch panel wall mount rack bracket supports 19" rack-mountable IT/AV/Network equipment of any depth; 150lb (68kg) capacity; EIA-310 and REACH Compliant; Compact design for minimal footprint in server room/closet
- **READY TO USE:** The wall mount vertical rack bracket ships fully assembled, and includes 6x Wood Screws, and 12x M5 Cage Nuts and Screws for mounting the rack and equipment; Two mounting holes support 16in wood stud spacing
- **BUILT TO LAST:** The vertical rack bracket is constructed with a 14-gauge steel frame; Provides a solid and stable anchor to mount equipment; The powder coated paint and interior corner welding ensures long-lasting use and sturdiness
- **CERTIFIED PACKAGING:** This assembled and ready-to-use patch panel rack bracket ships with ISTA-6 certified packaging that ensures damage-free delivery; This vertical wall mount rack bracket is TAA compliant
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this vertical wall mount patch panel bracket is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	3U
Special Features	Ships Fully Assembled
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	150.0 lb [68.0 kg]
-----------------	--------------------

Special Notes / Requirements

Note	Package includes screws for mounting to wood surfaces, additional hardware will be required for other materials
------	---

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements

Product Length	6.1 in [15.5 cm]
Product Width	19.9 in [50.5 cm]
Product Height	5.9 in [15.0 cm]
Weight of Product	2.0 lb [0.9 kg]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	6.9 in [17.6 cm]
Package Width	21.5 in [54.5 cm]
Package Height	6.7 in [17.1 cm]
Shipping (Package) Weight	3.3 lb [1.5 kg]

What's in the Box

Included in Package	1 - 3U Vertical Wall Mount Bracket
	12 - M5 Screws
	12 - M5 Cage Nuts
	6 - Wood Screws
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***