




Process adapters pipe fitting DIN11851

ADAPT DIN11851 DN80



Application		
Design	for volumetric flow meters SMF	
Application	food and beverage industry; hygienic systems	
Pressure rating	25 bar	2.5 MPa
Tests / approvals		
Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions	The compatibility between medium and product material has to be checked in all applications.	
Mechanical data		
Weight	[g]	4988.8
Materials	stainless steel (316L/1.4404)	
Nominal diameter	DN80 (3")	
Sensor connection	ifm-specific device flange	
Process connection	hygienic pipe fitting DIN 11851	

E40505



Process adapters pipe fitting DIN11851

ADAPT DIN11851 DN80

Process connection suitable for pipe standard	(DIN EN 10357 series A); (DIN 11866 series A); (DIN 11850 series 2)
Surface characteristics Ra/Rz of the wetted parts	Ra ≤ 0.4 µm
Accessories	
Items supplied	screws 12
Remarks	
Pack quantity	2 pcs.