

Steel Rod Cutter LXT®

DSC251

18V • 10 - 25 mm • 2 200 min⁻¹

Fast, nearly spark-free cutting of steel rods and rebars

A cutter designed for cutting steel rods and rebars. Max. cutting capacity of 25 mm, fine edge cutting (3,5 mm). A three-position removable side grip for added comfort.



LXT **BL** **ADT**
MOTOR

Technical specifications

Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	2200 min ⁻¹
Cutting Capacity Stainless Steel (up to 600N/mm ²)	10 - 25 mm
Blade Diameter	110 mm
Sound Pressure Level (L _{pA})	78 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Product Dimensions (L x W x H):	471 x 137 x 139 mm
Tool weight with battery	3,9 - 4,0 kg

User benefits

- Brushless maintenance-free and long-life motor
- No dust, no sparks.
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- 3-stage LED gauge indicates battery charge level / overheating / overload
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

■ Optional AC

153489-2
Grip complete 125 mm



SC09009190
Plastic carrying case



■ Other

User manual

Parts drawing