

Part Number : [524180610](#)

Product Description : 2.00mm Pitch SlimStack Board-to-Board Receptacle, Right-Angle, Single Row, Friction Lock, 6 Circuits

Series Number : 52418

Status : Obsolete

Product Category : Board-to-Board Connectors

Documents & Resources

Drawings

[524180610 sd.pdf](#)

[Symbol and Footprint \(Multi-Format\)](#)


Specifications

[524189200-SPK-200.pdf](#)

[PS-52418-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 47; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Board-to-Board Connectors
Series	52418
Description	2.00mm Pitch SlimStack Board-to-Board Receptacle, Right-Angle, Single Row, Friction Lock, 6 Circuits
Application	Board-to-Board, Signal
Component Type	PCB Receptacle
Product Name	SlimStack
UPC	800753567948

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Physical

Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	30
Glow-Wire Capable	No

Mated Height	3.95mm
Mated Width	6.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	288.900/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.914µm
Plating min - Termination	0.914µm
Polarized to PCB	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole - Kinked Pin

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.00mm Pitch Vertical SlimStack Plugs	<u>53290</u>