

TSI Code: 383547484

Price\*: 902.00 GBP



### Main

Range	Spacial
Product name	Spacial SD
Device application	Multi-purpose
Product or component type	Monobloc control desk with rear panel
Enclosure nominal height	1000 Mm
Enclosure nominal width	800 Mm
Enclosure nominal depth	597 Mm
Installation accessory type	Floor-standing
Device composition	1 structure 1 door 2 lock: door 4 adjustment rail 1 cable gland plate 2 pneumatic stay: desk lid 1 rear panel 3 top plate: on top of control desk

### Complementary

Body type	Single piece structure folded and welded
Door type	Plain
Number of doors	Front: 1 door(s)
Door opening side	Reversible 120 ° door
Lock type	2 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	1 entry plate
Accessibility for operation	Front Rear
Removable parts	Door by hinges Desk lid by hinges Cable gland plate by clipping screws Blanking covers by screws Rear panel by screws
Material	Body: steel
Surface finish	Epoxy-polyester powder
Thickness	1.5 Mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. \*Prices are indicative

## Environment

Standards	IEC 62208
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	58 Kg
Package 1 Height	114.5 Cm
Package 1 width	81.5 Cm
Package 1 Length	61.5 Cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**