

Technical data sheet

Article number:
924-00395

SD2-6

Product Group	Spade/Forks Terminals
Product Family	Double Grip Pre-Insulated
Material	Copper (CU), Polyvinylchloride (PVC)
Colour	Blue (BU)
Application Range	Low Voltage
Conductor Size Range mm²	1.5-2.5 mm ²
Diameter (D)	5.3 mm
for Hole Ø (FH)	6.4 mm
Length (L)	23 mm
Length (L2)	10.5 mm
Length (L3)	12.5 mm
Max Current	27 A
Max Voltage	600 V
Operating Temperature	+75 °C
Package Content	100 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	10.7 mm

RoHS 