

LONG LIFE CUTTING MEDIUM THICK TOUGH METAL

EXPERT 'Medium-Thick Tough Metal' Blades

EXPERT

- ① Exceptional durability is built in with Bosch Carbide Technology.
- ② Fine teeth cut thinner material with ease.
- ③ Wide body for precise, straight cuts.



* vs. Bosch S1122BF



BOSCH

EXPERT MEDIUM-THICK TOUGH METAL S955HHM BLADE



- ▶ Ideal for cutting tough metal pipes and profiles with medium wall thickness; capable of cutting stainless steel; and any hardened, high alloy or high strength steel
- ▶ Best for recycling and demolition workers: long lasting and powerful
- ▶ Lasts up to 50x longer than Bosch S1122BF blade in tough materials
- ▶ Fits all S-shank reciprocating saws



PRODUCT PROPERTIES							ORDERING INFORMATION				
Tooth spacing [mm]	Tooth pitch [TPI]	Dimensions LxWxT [mm]	Blade material abbreviation	Recommended min. material thickness [mm]	Recommended max. material thickness [mm]	Max. cut capacity [mm]	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
2.5	10	150 x 25 x 1	CT	3	8	100	C1c	1	1	534 633	2 608 900 373



BOSCH