

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Angle Grinder

GWS 18-125 V-LI Professional

from GBP 131.33*

* Price including VAT

The most powerful 18-volt angle grinder

The most important data

Battery voltage	18 V
No-load speed	10.000 rpm
Grinding/cutting disc, diameter	125 mm

Part number: 0 601 93A 307[> More product information](#)

Technical Data

Performance data

No-load speed	10.000 rpm
---------------	------------

Battery and power

Battery voltage	18 V
-----------------	------

Tools

Grinding/cutting disc, diameter	125 mm
Rubber backing pad, diameter	125 mm

Noise/vibration information

Surface grinding (roughing)

Vibration emission value ah	6,0 m/s ²
Uncertainty K	1,5 m/s ²

Sanding with sanding sheet

Vibration emission value ah	2,5 m/s ²
Uncertainty K	1,5 m/s ²

Noise

Sound pressure level	82 dB(A)
Sound power level	93 dB(A)
Uncertainty K	3 dB



Product data sheet

Power tools for trade & industry

Advantages

- Highest material removal rate and cutting performance in its class per battery charge
- Extremely robust and durable 4-pole high-performance motor for a long lifetime
- Compact design and low weight (only 2.3 kg) for comfortable working, especially in tight spaces and overhead
- Innovative COOLPACK batteries ensure optimum heat dissipation and therefore increase lifetime by up to 100% (cf. Li-Ion batteries without COOLPACK)
- Bosch Electronic Cell Protection (ECP): protects the battery against overload, overheating and deep discharge
- Bosch Electronic Motor Protection (EMP) protects the motor against overload and ensures a long lifetime

