



Part Number : [2133094700](#)

Product Description : Hand Crimp Tool for Micro-Fit+ Crimp Terminals, 24 AWG, UL 1007 and UL 1061 Wires

Series Number : 207129

Status : Active

Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

[2133094700-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for Micro-Fit+ Crimp Terminals, 24 AWG, UL 1007 and UL 1061 Wires
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Micro-Fit+
Tool Type	Hand Crimp Tool
UPC	195842807372
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Applicable Parts

Description	Part Number
Micro-Fit TPA Crimp Terminal, Male, with Tin (Sn) Pre-plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315003</u>
Micro-Fit TPA Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315004</u>
Micro-Fit TPA Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315005</u>
Micro-Fit TPA Crimp Terminal, Male, with 2.54µm Matte Tin Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315006</u>
Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 24-20 AWG	<u>2064600021</u>
Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 24-20 AWG	<u>2064600022</u>
Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 24-20 AWG	<u>2064600023</u>
Micro-Fit+ Crimp Terminal, Male, Matte Tin (Sn) Plating, 24-20 AWG	<u>2159530021</u>
Micro-Fit+ Crimp Terminal, Male, 0.38µm Gold (Au) Plating, 24-20 AWG	<u>2159530022</u>
Micro-Fit+ Crimp Terminal, Male, 0.75µm Gold (Au) Plating, 24-20 AWG	<u>2159530023</u>