



Product designation
Product type designation

Description

Accessories for

Motor operator
P5X193D024
Motor operator
for remote
operation.
Accessories for
IEC-compliant
MCCBs

Operational characteristics

Rated operational voltage	V	24VDC
Rated current (I _n)	A	≤5A
Mechanical operation	cycles/h	20
Average closing time	ms	700
Average opening time	ms	420
Power consumption	W	35


Mechanical features


Weight	g	3500
--------	---	------

Operations

Mechanical life	cycles	10000
-----------------	--------	-------

Dimensions





Note: Connect an NC contact of an alarm switch contact block in series with S4 to prevent remote closing of the MCCB after tripping due to overcurrent or short circuit.

Wiring diagrams

Certifications and compliance

Certificates

ETIM classification

EC000066 - Power contactor, AC switching