

# DD 2G 10.8-LDBC/2.5

2-speed cordless drill driver 10,8 V Light Duty

Order no. 516155

GTIN 4030293236387

- + Handy tool for easy drilling and screwdriving applications
- + Electronic management system (EMS) protects the machine, extends the service life, and increases efficiency
- + Electronic quick-acting brake
- + Accelerator trigger with lock-off switch
- + Right/left rotation with safety catch
- + Ergonomically designed, non-slip, soft grip handle
- + Integrated LED lamp with persistence function
- + LED battery capacity display
- + FLEX battery system: suitable for all FLEX 12 V battery packs



Throttle switch



Carrying case

## Technical data

Battery voltage	10.8 V
No-load speed, 1st gear	0 - 350 rpm
No-load speed, 2nd gear	0 - 1300 rpm
Max. torque, hard	34 Nm
Max. torque, soft	17 Nm
Max. drilling diameter in wood	25 mm
Max. drilling diameter in steel	10 mm
Chuck clamping width	0,8 - 10 mm
Number of supplied batteries	2 Cont.
With charger	Yes
Dimensions WxLxH	177 x 66 x 177 mm
Weight without battery pack	0.875 kg

## Standard equipment

- 1 Rapid charger 10.8 Volt (418021)
- 2 Li-Ion rechargeable battery pack 10,8 V (418048)
- 1 Carrying case