

02 0254

# Quicklock circular connectors, IP67





Quicklock plug with locking latch, IP67, size 28, straight version, with plastic housing and screw clamps (8-pole version with solder terminals)

1 of 4 05/2020



02 0254







0254 03

0254 08

0254 02

### **Environmental conditions**

Temperature range -40 °C/+80 °C

#### Materials

Insulating body PBT, V-0 according to UL94

Contact pin CuZn, gold-plated

PBT, V-0 according to UL94 F1 according to UL 746C, outdoor suitability (UV-light, immersion) Housing

Guiding element Zn alloy, chrome-plated

Zn-alloy, chrome-plated Locking PBT, V-0 according to UL94, F1 according to UL 746C Cap nut

Mechanical data

Protection class IP671  $^{\mbox{\scriptsize 1}}$  only in locked condition with an appropriate counterpart

# Connectable conductors for screw clamp

2.5-16.0 mm<sup>2</sup>/AWG 14-6 (2-3 Section

poles)

Cable diameter 4.0-11.5 mm

## Connectable conductors for solder area

1.5-4.0 mm<sup>2</sup>/AWG 16-12 (8 poles) Section

Cable diameter 4.0-11.5 mm

## Electrical data (at Tamb 20 °C)

Contact resistance ≤ 5 mΩ

Rated current

50 A (2 poles) 43 A (3 poles) 17 A (8 poles)

Rated voltage 500 V AC Rated impulse voltage ≤ 2500 V Creepage distance ≥ 2 mm Clearance ≥ 2 mm Insulation resistance > 500 MΩ

2 of 4 05/2020



02 0254

# Associated products

Counterparts ☑ 0264

**₫** 0274

3 of 4 05/2020





Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
0254 02	2	2	20
0254 03	3	2	20
0254 08	8	2	20

# Packaging:

in individual plastic bags, in a cardboard box

4 of 4 05/2020