



Part No. 112087103

Series 208 Detect blow guns

3D

PDF

[Inquiry List](#)

Class title

90 mm brass tube with Star-Tip

Tube

Fixed tube

Connection

Rc 1/4"

Noise level (db)

79 dB

Flow capacity (l/min)

190 l/min

Max working pressure (bar)

16 bar (232 PSI)

Standards

OSHA STD 01-13-001, OSHA 1910.95 (b) (c)

Min. burst pressure (bar)

64 bar (928 PSI)

Material

PA66 (body), brass (tube) Stainless steel (valve)

Media

Air

208 Detect blow guns

The 208 Detect blow gun, made of food-grade plastic, is developed to improve food safety. Its fully detectable components eliminate the risk of accidental contamination during the manufacturing process.



Check with an authorized CEJN distributor for availability and prices. All measurements are in mm. Other connections and sealing material on request. Some part numbers may be subject to minimum order quantities. CEJN reserves the right to make changes without further notification. Thread connections are listed according to ISO standards, unless stated otherwise.