

Powerpact 4 - Molded Case Circuit Breaker - 1P - 63A - 230 V - L1

Local distributor code: 386962257

MGP0631L1

! Discontinued on: 20 Mar 2023

EAN Code: 3606486440155

Main

Range of product	PowerPacT 4
Product or component type	Circuit breaker
Device application	Distribution
Poles description	1P
[In] rated current	63 A at 40 °C
[Ue] rated operational voltage	230 V AC 50/60 Hz
Suitability for isolation	Yes conforming to BS EN 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	25 kA Icu at 230 V AC 50/60 Hz
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit protection functions	П
control type	Toggle
Circuit breaker mounting mode	Panel-mounted

Complementary

[Ui] rated insulation voltage	750 V
[Uimp] rated impulse withstand voltage	8 kV
[lcs] rated service short-circuit breaking capacity	25 kA at 230 V AC 50/60 Hz
Mechanical durability	20000 cycles
Electrical durability	20000 cycles at 277 V In/2 10000 cycles at 277 V In
Mounting support	Backplate
Mounting position	Horizontal and vertical
Phase connection	L1
Number of modules	1 module(s)35 mm
Protection type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip unit rating	63 A at 40 °C
Thermal protection adjustment range	63 A
Earth-leakage protection	Without

Environment

Standards BS EN 60947-2

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

EU RoHS Directive

Compliant with Exemptions