

## Ha-EIZ4 EIZ4-1.0M/KETH



Image is for illustration purposes only. Please refer to product description.

Part number	72 MD M4M DM40 10K
Specification	Ha-EIZ4 EIZ4-1.0M/KETH
HARTING eCatalogue	<a href="https://harting.com/72MDM4MDM4010K">https://harting.com/72MDM4MDM4010K</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Straight
Connector 2	M12 D-coding Male Straight
Type of cable	Copper cable (round)

### Version

Cable length	1 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-35 ... +80 °C

### Material properties

Material (cable)	PVC
------------------	-----



**Pushing Performance**  
Since 1945

## Material properties

Colour (cable) Green

---

## Specifications and approvals

Approvals CE

PROFINET Yes

---

## Commercial data

Packaging size 1

Country of origin China

European customs tariff number 85444290

GTIN 5713140247284

eCl@ss 27060390 Ready-made data cable (unspecified)

ETIM EC002599

UNSPSC 24.0 26121600