









Peli Storm Case Quick Comparison

Case	Rs Stock No.	Dimensions (cm)		Depth (cm)		Weight w/o Foam (kg)	Buoyancy Max. (kg)	Range Temperature Min. / Max.	Wheels
		Ext.	Int.	Lid	Case				
 iM2075	811-2072	30,0 x 24,9 x 19,6	24,1 x 19,1 x 18,4	3,8	14,6	1,50 kg	12,90	-29°C / 60°C	
 iM2100	811-2075	36,1 x 29,0 x 16,5	33,0 x 23,4 x 15,2	5,1	10,2	1,91 kg	15,34	-29°C / 60°C	
 iM2370	811-2079	50,8 x 37,4 x 14,7	46,2 x 30,7 x 13,2	4,3	8,9	2,59 kg	25,68	-29°C / 60°C	
 iM2400	811-2088	48,8 x 38,6 x 18,5	45,7 x 33,0 x 17,0	5,1	11,9	2,95 kg	31,96	-29°C / 60°C	
 iM2720	811-2081	62,5 x 50,1 x 29,7	55,9 x 43,2 x 25,4	5,1	20,3	7,62 kg	85,30	-29°C / 60°C	2
 iM3300	811-2085	136,7 x 41,9 x 17,0	128,3 x 35,6 x 15,2	5,1	10,2	8,66 kg	88,85	-29°C / 60°C	2