

Rexel Optimum AutoFeed+ 150X Automatic Cross Cut Paper Shredder

The Optimum AutoFeed+ 150X cross cut shredder automatically shreds up to 150x A4 sheets of paper (80gsm) at a time, into P-4 (4x28mm) cross cut pieces. This auto feed shredder machine is a sophisticated office shredder, featuring a 44L pull out bin. No need to manually feed paper, or remove staples and paper clips first, this automatic paper shredder will do all the work for you.



Attributes

- Auto feed up to 150 sheets of A4 paper (80gsm) at a time. Manual slot for up to 8 sheets.
- P-4 cross cut (4x28mm)
- 44L capacity pull out bin
- Anti-jam technology
- Shreds credit cards, staples and paper clips
- 30 minutes continuous run time with fan cooling. Sleep mode activates after 3 minutes of non use.
- Touch control panel
- 55 dBA ultra-quiet noise level
- Infra red bin full sensor
- 2 year warranty, 2 year cutter warranty



Specifications

Number	2020150X
Colour	black
Dimensions (W x H x D)	365 x 618 x 430 mm
Cut Type	Cross Cut
Maximum Slot Entry Width (mm)	220
Run Time From Cold (min)	30
Shredded Particle Width mm	4x28
Security Level	P-4
Cutting Capacity sheets (70gsm paper)	165
Cutting Capacity sheets (80gsm paper)	150
Container/collection volume in l	44
Shreds	Paper, Credit cards, Paper clips & Staples
Power consumption (W)	300
Noise Level (dBA)	55
Period of Warranty (Years)	2
Location	Small Office
Number Of Users	1-5
Weight	15340 g
Pallet quantity	6
EAN code	5028252606257