

D


C

B

A


4

4



Front view


8.12



Isometric view


3

3



Top view

PU foam tape 0.4mm



Bottom view

2

2


INDEX	PART NO	DESCRIPTION	MATERIAL	COLOUR
1	CA13837	STRADA-SQ-T-DWC	PMMA	

Tolerances if not otherwise shown
According to DIN ISO 2768-1
Linear measures:
up to 30mm class M, otherwise class C
According to DIN ISO 2768-2
Form and position: class L

LEDiL

Ledil Oy
Salorankatu 10
FIN 24240 SALO
Finland

THIRD ANGLE PROJECTION:



DRAWING TITLE

CA13837_STRADA-SQ-T-DWC

This drawing is the property
of LEDiL Oy. It may not be
reproduced, copied or
communicated without a written
agreement with LEDiL Oy.

SIZE PART NUMBER

A4

CA13837

SCALE

2:1

WEIGHT

2,7 g

SHEET

1/1

1

1

D

A