

Product type designation

RF340T transponder

SIMATIC RF300 Transponder RF340T 8 KB FRAM, IP67/X9K, -25 to +85 °C, 48x2 5x 15 mm, Minimum order quantity 5 units



Suitability for operation

RF300

Radio frequencies	
Operating frequency / Rated value	13.56 MHz
Range / maximum	105 mm; range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964
Protocol / with radio transmission	RF300-specific
Transfer rate / with radio transmission / maximum	106 kbit/s
Product feature / multitag-capable	Yes

Electrical data	
Product component / Backup battery	No
Type of memory	FRAM / EEPROM
Storage capacity / of the user memory	8189 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 8189 bytes, OTP memory 20 bytes
Number of read cycles / at ambient temperature < 40 °C / maximum	10000000000
Number of write cycles / at ambient temperature < 40 °C / maximum	10000000000

Data retention time / at ambient temperature < 40 °C / not less than	10 y
Property of memory	Block-by-block write protection of the OTP memory

Mechanical data

Material	PA12
Color	anthracite
Mounting distance / relating to metal surfaces / recommended / minimum	0 mm

Ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during read/write access 	-25 ... +85 °C
<ul style="list-style-type: none"> outside the read/write area 	-40 ... +85 °C
<ul style="list-style-type: none"> during storage 	-40 ... +85 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²

Design, dimensions and weight

Width	25 mm
Height	15 mm
Depth	48 mm
Net weight	25 g
Mounting type	2 x M3 screws

Product features, product functions, product components / general

Product feature	
<ul style="list-style-type: none"> silicon-free 	Yes
<ul style="list-style-type: none"> printable 	No

Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> IECEX 	No
MTBF	1200 y

Further information / Internet-Links

Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL 	https://support.industry.siemens.com/cs/ww/en/view/67384964
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/ident/rfid
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAx Download Manager 	http://www.siemens.com/cax

- to website: Industry Online Support

<https://support.industry.siemens.com>

last modified:

12/14/2019