



AS SC-2345S2 TL26



AS SC-2345S2 TL26

E1441331

Assortment box of 300pcs, Releasable Splicing connectors & Terminal Blocks

Product Properties:

Nominal voltage	450 V
Nominal current	32 A
Transparent	Yes
Number of clamp positions	2-5 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Colour	Green

Dimensions:

Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-4 mm²
Conductor cross section solid (solid, stranded)	0.2-4 mm²

MOQ	1 .
Unit	pcs
Nominal cross section	0.2-4 mm ²
AWG-range	28-12 .
Nominal voltage	450 V

Approvals:

Compliance:

REACH	No SVHC (Latest. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Splicing Connectors - Assortment Boxes
Search Description	SKV2024ERIK3 ENR2023H
Alternative SKU	ASSC-2345S2TL26
E-no	E1441331

Logistic information:

Barcode	733117641340
Country of origin	CN
E-no	E1441331
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	AS SC-2345S2 TL26
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.